

EDDYFI REDDY

First Portable System for AC and ECT Tubing Inspection



MADE FOR AC AND ECT TUBING INSPECTIONS.

This version of Reddy® is designed to replace a wide range of aging ECT instruments used to inspect air conditioners and perform other ECT tubing inspections. Existing ECT instruments are unwieldy and have evolved very little since their introduction, making them incompatible with modern inspection conditions where productivity and profitability are crucial.

DESIGNED FOR ACS

Reddy is designed to support all current AC and ECT probes on the market without adapters or reference probes to balance the absolute channel. No other portable system is battery-operated or sealed, or features a large display, automated acquisition sequences, or an analysis software for on-the-fly reporting. Furthermore, data recorded with Reddy is compatible with the industry-standard TubePro tubesheet mapping-reporting software for in-depth analysis.

PORTABLE AND INTUITIVE

Because air conditioners are similar to small heat exchangers (HX) in terms of number of tubes, for example, portability and minimal setup time are essential. Reddy is roughly 30% lighter than the most widespread instruments currently in the field, and it features probe plug-and-play capabilities and a setup wizard for increased productivity.

MASSIVE MULTI-TOUCH DISPLAY

The premium-quality 26.4 cm (10.4 in) LED display is optically bonded, non-reflective, and comes with 3 mm (1/8 in) strengthened glass. It's designed for gloved hands and all lighting conditions. The multi-touch capabilities make it easy to zoom and rotate views.

DESIGNED FOR FIELD USE

Reddy is sealed and designed to IP65 requirements. The magnesium alloy casing is heavy-duty, cools without fans or external airflow, and is water and dust resistant. The adjustable stand and the top handle only add to the system's practicality in on-site inspections.



CONFIDENCE IN YOUR RESULTS WITH POWERFUL REPORTING

Reddy combines on-the-spot data acquisition, recording, and management completely doing away with handwritten reports. When an inspection is complete, reports can be generated in a single click—complete with screenshots of detected defects—signed, and handed to customers.

OPTIMIZED INSPECTION TIME

Automated acquisition sequences are a huge time saver, because they minimize the number of required operations to perform a complete inspection, such as starting and stopping the acquisition, recording data, and using foot pedals. Eddyfi Magnifi® GO also allows you to create tube lists, and features a dedicated setup wizard, automated data recording sequences, and a unique reporting format further enhancing productivity

MODERN COMPUTER CAPABILITIES

Equipped with a robust, 100GB internal solid-state disk drive (SSD) for secure inspection data. The embedded system offers standard connect-anywhere capabilities and advanced productivity tools optimizing field testing.

EMBEDDED PC CAPABILITIES

Magnifi GO, Eddyfi's powerful and easy-to-use acquisition / analysis software, is tailored for air-conditioner and tubing inspections, and has a well-designed wizard to create setups. Furthermore, Magnifi GO makes collecting and reporting data incredibly intuitive. Fast, from setup to reporting. If these standard probes don't meet your specific requirements, you can still leverage the full might of Reddy—Eddyfi Technologies experts can design custom probes to suit your exact needs.

DESKTOP DATA ANALYSIS

Magnifi GO is compatible with its full-fledged big brother Magnifi R. You can configure inspection setups for Reddy and perform in-depth inspection data analysis on your desktop or laptop computer.

WWW.EDDYFI.COM/REDDY-FOR-TUBING-INSPECTION/



SPECIFICATIONS

INSTRUMENT		
Dimensions (W×H×D)		355×288×127 mm (14.0×11.3×5.0 in)
Weight	With batteries	6.6 kg (14.5 lb)
Volume		13 L (791 in ³)
Power requirements		100–240 VAC, 50–60 Hz
Power supply		Direct VAC or onboard batteries
Maximum input current		1.5 A
Batteries	Type	Li-ion, rechargeable, DOT compliant
	Typical life	6–8 hours
Video output		HDMI
Temperature	Operating	0–40 °C (32–104 °F)
	Storage	–20–60 °C (–4–140 °F)
	Humidity	95 %, non-condensing

ECA/ECT (CONT.)	
Frequency range	5 Hz–10 MHz
ECT BOBBIN/AC connectors	4 pins
I/O connector	18 pins
Dedicated connector	30 pins
Generator output / Coil drive	Up to 20 Vpp
Injection modes	Simultaneous, continuous
Receiver gain	41 dB range, 23–64 dB
Data resolution	16 bits
Acquisition / Sampling rate	Up to 50 000 samples/s

INSTRUMENT (CONT.)	
Storage	SSD, 100 GB
Display	26.4 cm (10.4 in) Non-reflective (AR coating) Anti-fingerprint (oleophobic coating) 3 mm (1/8 in), chemically strengthened glass cover Optically bonded LCD and touchscreen Passive backlight enhancement
Cooling	Sealed and fanless
Connectivity	Gigabit Ethernet, Wi-Fi, Dual Mode Bluetooth® 2.1, 2.1+EDR, 3.0, 3.0+HS, 4.0 (BLE), USB 2.0 (×3)
IP rating	Designed for IP65
Pollution rating	2
Compliance	ASME, EN 61010-1, CE, WEEE, FCC Part 15B, ICES-003, AS/NZS CISPR 22, RoHS

The information in this document is accurate as of its publication. Actual products may differ from those presented herein.

©2018 Eddyfi NDT, Inc. Eddyfi, Magnifi, Reddy, SmartMUX, and their associated logos are trademarks or registered trademarks of Eddyfi NDT, Inc. in the United States and/or other countries. Eddyfi Technologies reserves the right to change product offerings and specifications without notice.

2018-10-03

www.eddyfi.com

info@eddyfi.com